

CERTIFICATE OF COMPLIANCE



Date of issue: 15 June 2021

Valid until: 31 December 2022

EL Class I

EHEDG hereby declares that the product

inline refractometer, type L-Rix 4100 Transmitter, L-Rix 5000, L-Rix 5100, L-Rix 5200 and Fermentation Monitor 5100 with PEEK gasket

from

Anton Paar GmbH, Anton-Paar Str. 20 , 8054 Graz, Austria

has/have been evaluated for compliance and meets/meet the current criteria for Hygienic Equipment Design of the EHEDG

Certificate No. EHEDG-C2100016

Signed

Ludvig Josefsberg

President EHEDG

Signed

Karlijn Faber

EHEDG Certification Officer

*EHEDG
Gooimeer 1
1411 DC Naarden
Netherlands*

©EHEDG



Appendix 3

EHEDG Certification – Equipment Evaluation Form

Design Evaluation Date: 23.04.2021

EHEDG File Number: EHEDG-C2100016

Certification Type: EL CLASS I

Applicant: Anton Paar GmbH

Equipment: inline refractometer, type L-Rix 4100 Transmitter, L-Rix 5000, L-Rix 5100, L-Rix 5200 and Fermentation Monitor 5100 with PEEK gasket

Other essential identification:

Evaluated by:

Name: Dr. Jürgen Hofmann

Approved by:

Name: Alan Friis

Title: AEO

Date, Signature: 08.06.2021 

<p>1. Results of inspection for compliance with the EHEDG Hygienic Design Criteria. Conclusion:</p> <p>The equipment complies with the criteria.</p> <p>The use of the EHEDG Certification logo is justified:</p>	<p>YES <input type="checkbox"/></p> <p>MAYBE <input checked="" type="checkbox"/></p>
<p>2. Evidence for compliance provided and convincing for Certification. Conclusion:</p> <p>The equipment complies with the criteria where possible.</p> <p>The use of the EHEDG Certification logo is justified:</p>	<p>YES <input checked="" type="checkbox"/></p>

Signature: 

Date: 27.05.2021

The original of this form will be kept by EHEDG together with the application, the inspection report, the evidence provided and any other relevant documentation, as listed on the list

Appendix 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the inline refractometer, type L-Rix 4100 Transmitter, L-Rix 5000, L-Rix 5100, L-Rix 5200 and Fermentation Monitor 5100 with PEEK gasket, no. 664TUM2021
7.	Drawing of the inline refractometer, type L-Rix 4100 Transmitter, L-Rix 5000, L-Rix 5100, L-Rix 5200 and Fermentation Monitor 5100 with PEEK gasket, drawing no. d32mz0034_ehedg; original stamped
8.	Test report of the in-place cleanability test method, no. 664/21.12.2018
9.	Cleaning and Installation manual provided by the equipment supplier
10.	Example of EHEDG Certified Logo Type EL CLASS I